


! Pin screw for additional locking of the fiber ferrule:  
 - before pulling the FC-connector:  
 unlock the pin screw.  
 - before inserting the FC-connector:  
 make sure the ferrule receptacle is not blocked  
 by the pin screw !

clamp screws  
 for accessory optics (3x120°)  
 using hex-key size 1.5mm  
 50HD-15 ①



A-A  
 clamp screws for adjustment  
 fiber collimator (2x120°)  
 using hex-key size 1.5mm  
 50HD-15 ①



clamp screws for locking focus setting (2x120°)  
 using hex-key size 1.5mm  
 50HD-15 ①

Fiber receptacle  
 type FC-PC  
 (wide key)



! Don't touch any other screws !



Tools for assembly and adjustment

hex-key  
 size 1.5mm  
 50HD-15

screw driver  
 size 1.2mm  
 9D-12



Allgemeintoleranz ISO 2768 - f		Maßstab: 2:1
60FC-L-0-M35-xx 60FC-L-0-M40-xx		
Datum 27.07.2017		Name
Gepr.		
Norm		
Schäfter&Kirchhoff OPTO-SENSORIK UND MESSTECHNIK OPTIK-ENTWICKLUNG/ELEKTRONIK/SENSORTECHNIK/SOFTWARE		Fiber Collimator f'35-40
Datei: 951210190133.idw		9512-1019-0133
Zust.		Blatt A3
Änderungen		Blatt 1
Datum		Modell: 951210190133.iam
Name		